

Phonak Roger TableMic II Twin Pack



Description

A flexible and intelligent wireless microphone designed for working adults with a hearing loss who participate in small and large meetings.

The microphone is easily connected to the receiver/s (not included) with a simple touch of a button and when placed on a table it wirelessly transmits speech to a hearing aid.

Roger Table Mic II features MultiBeam Technology, an innovative Roger microphone technology from Phonak. By utilising multiple microphones, beams are created in six directions to cover 360°. The signal-to-noise ratio for all six directions is calculated and the beam with the best clarity is automatically selected. Providing exceptional speech understanding in group conversations such as in noisy restaurants or family gatherings.

The Roger Table Mic II is used with miniature Roger receivers, which attach directly to hearing aids or cochlear implants.

Features

- Audio processing fine-tuned for meetings
- Easy coverage of large meetings with MultiTalker Network
- Remote control for increased convenience
- 3.5mm audio input for connection to multimedia devices
- 20 hours of operating time
- Mute function

Roger Table Mic can be used in a multi-talker network along with:

- Several Roger Table Mics
- Roger Select
- Roger Pen and Roger EasyPen
- Clip-On Mic

The microphone transmits the meeting participants' voices directly into your ears. The system consists of three main elements: the hearing aids, Roger receivers and one or more Roger Table Mic(s). You can also connect the Roger Table Mic to an audio source – such as a conference telephone, tablet or computer - to hear its audio signal directly in your hearing aids.

Roger Table Mic includes: 1 x Roger Table Mic II, remote control, Power supply with country adaptor and charging cable (micro-USB), soft case, 3.5mm audio cable, RCA/Cinch adapter, quick setup guide

Technical information

- Size 69 x 69 x 14mm / 2.7" x 2.7" x 0.6" (approx)
- Weight 103 g / 3.63 oz
- Battery: Lithium polymer 3.7 V
- Operating time: Approx. 16 hours
- Operating range: 20m/66 feet (typical), 40m/130 feet (ideal conditions)
- Compatible Roger microphones: Roger Select, EasyPen, Roger Pen and Roger Clip-On Mic
- Omni directional microphone